

VT M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Reacts from a distance of 4 mm
- for testing operation of solenoid valves, relays, coils and contactors
- all magnetic fields can be tested
- Visual and acoustic indication
- including a flashlight function

General ordering data

| | |
|------------|--|
| Version | Testing tools, Non-contact magnetic field tester |
| Order No. | 2436680000 |
| Type | VT M |
| GTIN (EAN) | 4050118450019 |
| Qty. | 1 items |

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Length | 155 mm | Length (inches) | 6.1024 inch |
| Net weight | 55.7 g | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 7cl |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | |
|------------------------|-----------------------------------|
| Description of article | Non-contact magnetic field tester |
|------------------------|-----------------------------------|

Measuring and testing devices

| | | | |
|--------------|------------------------|----------------------------------|------------------------------|
| Display | Visual & acoustic | Protection degree | IP65 |
| Battery type | 1.5 V type AAA battery | Tested and approved according to | DIN EN 61010-1, DIN EN 61326 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000494 | ETIM 9.0 | EC000494 |
| ETIM 10.0 | EC000494 | ECLASS 14.0 | 27-20-03-08 |
| ECLASS 15.0 | 27-20-03-08 | | |