

VT M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Reacts from a distance of 4 mm
- for testing operation of solenoid valves, relays, coils and contactors
- all magnetic fields can be tested
- Visual and acoustic indication
- including a flashlight function

General ordering data

Version	Testing tools, Non-contact magnetic field tester
Order No.	2436680000
Type	VT M
GTIN (EAN)	4050118450019
Qty.	1 items

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Length	155 mm	Length (inches)	6.1024 inch
Net weight	55.7 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	No SVHC above 0.1 wt%
SCIP	b05b5 122-6 1 17-4cb0-b28c-df32f92 1fa36

Technical data

Description of article Non-contact magnetic field tester

Measuring and testing devices

Display	Visual & acoustic	Protection degree	IP65
Battery type	1.5 V type AAA battery	Tested and approved according to	DIN EN 61010-1, DIN EN 61326

Classifications

ETIM 8.0	EC000494	ETIM 9.0	EC000494
ETIM 10.0	EC000494	ECLASS 14.0	27-20-03-08
ECLASS 15.0	27-20-03-08		