

VT CTL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The fully insulated plastic housings of our continuity testers are shockproof and unbreakable, making these instruments ideal for daily use, even in tough conditions. The integrated torch makes it easier to locate defective cables quickly and safely. The results of the continuity test can be conveyed visually and acoustically.

General ordering data

Version	Testing tools, Testing device
Order No.	2436690000
Type	VT CTL
GTIN (EAN)	4050118450040
Qty.	1 items

VT CTL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 143.5 g

Environmental Product Compliance

RoHS Compliance Status Compliant
 RoHS Exemption (if applicable/known) 7cl
 REACH SVHC No SVHC above 0.1 wt%
 SCIP b05b5 122-6117-4cb0-b28c-df32f921fa36

Technical data

Description of article Continuity testers

Measuring and testing devices

AC voltage measuring range	0.1 - 400 V	Display	Visual & acoustic
Protection degree	IP44	Battery type	1.5 V type AAA battery
Continuity test	Yes - optical + buzzer	Tested and approved according to	DIN EN 61010-1

Classifications

ETIM 8.0	EC000494	ETIM 9.0	EC000494
ETIM 10.0	EC000494	ECLASS 14.0	27-20-03-08
ECLASS 15.0	27-20-03-08		

VT CTL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

