


HS 1.6-4.8/50 MM W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|------------|---|
| Version | Conductor and cable markers, 1.6 - 4.8 mm, 50.8 x 7.6 mm, white |
| Order No. | 2437570000 |
| Type | HS 1.6-4.8/50 MM W |
| GTIN (EAN) | 4050118461077 |
| Qty. | 1000 items |

HS 1.6-4.8/50 MM W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.77 mm | Depth (inches) | 0.0303 inch |
| Height | 50.8 mm | Height (inches) | 2 inch |
| Width | 7.6 mm | Width (inches) | 0.2992 inch |
| Net weight | 0.6 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...135 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|---|-----------------------------------|--|
| Type of printing | neutral | Width | 7.6 mm |
| Operating temperature range, max. | 135 °C | Operating temperature range, min. | -55 °C |
| Colour | white | Halogen | Yes |
| Basic material | Polyolefine | Printed characters | without |
| Recommended industries | Plant manufacture, Energy, Device manufacturer, Machinery | compatible printer | THM MULTIMARK , THM MULTIMARK PLUS |
| Operating temperature range | -55...135 °C | Number per roll | 1000 |

Conductor and cable markers

| | | | |
|-----------------------------------|--------------------------|-------------------------------|-------------------|
| Halogen | Yes | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 0.75 mm ² | Conductor O.D., max. | 4.8 mm |
| Conductor O.D., min. | 1.6 mm | Rate of shrinkage | 3:1 |
| Recommended shrinking temperature | 90 °C | Conductor O.D. | 1.6 - 4.8 mm |
| Cross-section for connected wire | 0.75 - 4 mm ² | | |

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

HS 1.6-4.8/50 MM W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HS 1.6-4.8/50 MM W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|------------|--|
| Type | RIBBON MM-HS 60/300 SW | Version | |
| Order No. | 2448880000 | Ink ribbon | |
| GTIN (EAN) | 4050118462944 | | |
| Qty. | 1 ST | | |

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK ROLLER 115 | Version | |
| Order No. | 1357420000 | | |
| GTIN (EAN) | 4050118160314 | | |
| Qty. | 1 ST | | |

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK PLUS ROLLER 1... | Version | |
| Order No. | 2672590000 | | |
| GTIN (EAN) | 4050118708097 | | |
| Qty. | 1 ST | | |