


HS 8.5-25.4/25 MM Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 8.5 - 25.4 mm, 25.4 x 40.5 mm, yellow
Order No.	2437800000
Type	HS 8.5-25.4/25 MM Y
GTIN (EAN)	4050118460964
Qty.	400 items

HS 8.5-25.4/25 MM Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Height	25.4 mm	Height (inches)	1 inch
Width	40.5 mm	Width (inches)	1.5945 inch
Net weight	1.6 g		

Temperatures

Operating temperature range	-55...135 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	40.5 mm
Operating temperature range, max.	135 °C	Operating temperature range, min.	-55 °C
Colour	yellow	Halogen	Yes
Basic material	Polyolefine	Printed characters	without
Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery	compatible printer	THM MULTIMARK , THM MULTIMARK PLUS
Operating temperature range	-55...135 °C	Number per roll	400

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	35 mm ²	Conductor O.D., max.	25.4 mm
Conductor O.D., min.	8.5 mm	Rate of shrinkage	3:1
Recommended shrinking temperature	90 °C	Conductor O.D.	8.5 - 25.4 mm
Cross-section for connected wire	35 - 120 mm ²		

Classifications


ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

HS 8.5-25.4/25 MM Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HS 8.5-25.4/25 MM Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM-HS 60/300 SW	Version	
Order No.	2448880000	Ink ribbon	
GTIN (EAN)	4050118462944		
Qty.	1 ST		

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK ROLLER 115	Version	
Order No.	1357420000		
GTIN (EAN)	4050118160314		
Qty.	1 ST		

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version	
Order No.	2672590000		
GTIN (EAN)	4050118708097		
Qty.	1 ST		