


HS-HF 19.5-38.1/25 MM W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 19.5 - 38.1 mm, 25.4 x 60.5 mm, white
Order No.	2437950000
Type	HS-HF 19.5-38.1/25 MM W
GTIN (EAN)	4050118460681
Qty.	200 items

HS-HF 19.5-38.1/25 MM W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Height	25.4 mm	Height (inches)	1 inch
Width	60.5 mm	Width (inches)	2.3819 inch
Net weight	3.2 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	60.5 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Colour	white	Halogen	No
Basic material	Polyolefine	Printed characters	without
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS	Operating temperature range	-55...105 °C
Number per roll	200		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	240 mm ²
Conductor cross-section, min.	70 mm ²	Conductor O.D., max.	38.1 mm
Conductor O.D., min.	19.5 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	19.5 - 38.1 mm
Cross-section for connected wire	70 - 240 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

HS-HF 19.5-38.1/25 MM W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

