

HS-HF 6.4-12.7/25 MM B**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 6.4 - 12.7 mm, 25.4 x 20.9 mm, blue
Order No.	2438130000
Type	HS-HF 6.4-12.7/25 MM B
GTIN (EAN)	4050118461220
Qty.	1000 items
Delivery status	This article will no longer be available in the future.
Available until	2025-08-31T00:00:00+02:00

HS-HF 6.4-12.7/25 MM B

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Height	25.4 mm	Height (inches)	1 inch
Width	20.9 mm	Width (inches)	0.8228 inch
Net weight	0.6 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	20.9 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Colour	blue	Halogen	No
Basic material	Polyolefine	Printed characters	without
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS	Operating temperature range	-55...105 °C
Number per roll	1000		


Conductor and cable markers

Halogen	No	Conductor cross-section, max.	35 mm ²
Conductor cross-section, min.	6 mm ²	Conductor O.D., max.	12.7 mm
Conductor O.D., min.	6.4 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	6.4 - 12.7 mm
Cross-section for connected wire	6 - 35 mm ²		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings



HS-HF 6.4-12.7/25 MM B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Ink ribbons




These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM-HS 60/300 SW	Version	
Order No.	2448880000	Ink ribbon	
GTIN (EAN)	4050118462944		
Qty.	1 ST		

THM MULTIMARK




These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK ROLLER 115	Version	
Order No.	1357420000		
GTIN (EAN)	4050118160314		
Qty.	1 ST		

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version	
Order No.	2672590000		
GTIN (EAN)	4050118708097		
Qty.	1 ST		