


HS-HF 6.4-12.7/50 MM Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|------------|---|
| Version | Conductor markers, Conductor and cable markers, 6.4 - 12.7 mm, 50.8 x 20.9 mm, yellow |
| Order No. | 2438170000 |
| Type | HS-HF 6.4-12.7/50 MM Y |
| GTIN (EAN) | 4050118460919 |
| Qty. | 500 items |

HS-HF 6.4-12.7/50 MM Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.77 mm | Depth (inches) | 0.0303 inch |
| Height | 50.8 mm | Height (inches) | 2 inch |
| Width | 20.9 mm | Width (inches) | 0.8228 inch |
| Net weight | 1.3 g | | |

Temperatures

Operating temperature range -55...105 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|-----------------------------------|--|-----------------------------------|--------------|
| Type of printing | neutral | Width | 20.9 mm |
| Operating temperature range, max. | 105 °C | Operating temperature range, min. | -55 °C |
| Colour | yellow | Halogen | No |
| Basic material | Polyolefine | Printed characters | without |
| compatible printer | THM MULTIMARK , THM MULTIMARK PLUS | Operating temperature range | -55...105 °C |
| Number per roll | 500 | | |

Conductor and cable markers

| | | | |
|-----------------------------------|------------------------|-------------------------------|--------------------|
| Halogen | No | Conductor cross-section, max. | 35 mm ² |
| Conductor cross-section, min. | 6 mm ² | Conductor O.D., max. | 12.7 mm |
| Conductor O.D., min. | 6.4 mm | Rate of shrinkage | 2:1 |
| Recommended shrinking temperature | 90 °C | Conductor O.D. | 6.4 - 12.7 mm |
| Cross-section for connected wire | 6 - 35 mm ² | | |

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

HS-HF 6.4-12.7/50 MM Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HS-HF 6.4-12.7/50 MM Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|------------|--|
| Type | RIBBON MM-HS 60/300 SW | Version | |
| Order No. | 2448880000 | Ink ribbon | |
| GTIN (EAN) | 4050118462944 | | |
| Qty. | 1 ST | | |

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK ROLLER 115 | Version | |
| Order No. | 1357420000 | | |
| GTIN (EAN) | 4050118160314 | | |
| Qty. | 1 ST | | |

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK PLUS ROLLER 1... | Version | |
| Order No. | 2672590000 | | |
| GTIN (EAN) | 4050118708097 | | |
| Qty. | 1 ST | | |