

## U-LINK-LIC-VPN-1Y

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Example of use



The Weidmüller u-link remote access service offers an easy possibility to securely access ethernet devices in a remote network.

With the u-link VPN Server as the central meeting point server, the VPN clients (service PC and Weidmüller u-link client devices) always connect outbound and thus conform to the typical IT security requirements.

Separate database and server instances are used for each u-link customer account (secure client isolation) to ensure data integrity.

Communication between the u-link VPN server and remote clients (service PCs and u-link client devices) takes place via a certificate-protected openVPN connection. The u-link creed is "configuration instead of programming" the use is intuitive and does not require expert knowledge.

#### Featureset:

- 1-click VPN remote access for service PC's
- easyAccess: web, rdp or vnc connections to remote hosts fully browser based for use with tablet or smartphone
- Organization and Group Management
- Topologies including 3rd party end-devices
- Firmware management: Display of firmware status of all routers and the option of a time-controlled, automated firmware update
- Individual access rights: granular configuration of access rights to devices in the target network

- Extensive event log: Presentation of all activities in the u-link portal with extensive filter and export functions
- Password policy: Increased security through configurable specification of minimum requirements for password quality and validity period

Weidmüller offers the following usage variations and additional options for the u-link Remote Access Service:

#### Basic version:

- Automatically assigned by registering at [u-link.weidmueller.com](http://u-link.weidmueller.com)
- Free use for 6 months, extended to 365 days when registering a new u-link client device
- Full featureset
- Unlimited users
- Max. 50 u-link capable devices (access points to a remote network)
- 1 simultaneous VPN connection
- No data or speed limitations (subject to normal market usage)

#### Extensions

- Additional 50/100/250/500/1000 or more u-link capable devices
- Additional simultaneous VPN connections
- China-VPN: secure and reliable VPN connection to and from China

## U-LINK-LIC-VPN-1Y

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

---

### General ordering data

Version	"VPN connection" licence code for u-link Remote Access Service. Can be used as an additional VPN connection or to extend the period of a VPN connection that has already been activated
Order No.	<a href="#">2447060000</a>
Type	U-LINK-LIC-VPN-1Y
GTIN (EAN)	4050118461497
Qty.	1 items
Delivery status	Discontinued
Available until	2023-03-17T00:00:00+01:00

## U-LINK-LIC-VPN-1Y

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	73 g
------------	------

## Temperatures

Storage temperature	Operating temperature
---------------------	-----------------------

## Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

## Functions and features

Extension of data volume	Data volume of the u-link client account increased by 1 GB/month with a bandwidth of 1 Mbit/s	Number of additional VPN connections (per licence code)	1 (pass-through VPN connection for service PC <-> u-link <-> router/target network)
VPN channel bandwidth	1 Mbit/s	Period	1 year from activation of the licence key. When extending a VPN licence that has already been activated, the validity period is extended by 1 year from the expiry date of the current period, but not less than 1 year.
Usage	Use as additional VPN channel or to extend period of a VPN channel. Can be used for all standard versions (not for entry version).		

## System requirements

Hardware, remote target network	Weidmüller router (except IE-SR-2GT-LAN-FN; 1489940000), u-link VPN access integrated in firmware (from V3.0.1)	Hardware (service PC)	PC with operating system Windows 7, 8 or 10
Portal administration (user/device configuration)	Standard browser (IE, Edge, Chrome, Firefox) via an HTTPS connection (SSL), login via username and password	VPN software (service PC)	u-link VPN-client (installation on PC)

## Miscellaneous

Activation	Client account administrator enters the licence key in the u-link portal (functions immediately available)	Included in delivery	Letter with licence key
------------	--	----------------------	-------------------------

## Classifications

ETIM 8.0	EC000809	ETIM 9.0	EC000809
ETIM 10.0	EC000809	ECLASS 14.0	27-24-25-01
ECLASS 15.0	27-24-25-01		

## U-LINK-LIC-VPN-1Y

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

## Industrial Security Router



## Weidmüller Industrial Security Routers

- Secure networks
  - Stateful packet inspection Firewall
  - IP/Port- forwarding
  - Network segmentation
- Easy integration of machine networks into manufacturing networks through 1: 1 NAT
- Secure and easy remote maintenance with Weidmüller u-link remote access service
- Enable modular and future proof network architectures with static and dynamic routing
- Secure communication over the Internet by using IPsec and OpenVPN
- Reliable internet connection, even without on-site internet access, thanks to integrated 4G/LTE cellular modem
- Full flexibility thanks to Fast Ethernet and Gigabit Ethernet interfaces ranging from 2 up to 4 ports.

## General ordering data

Type	IE-SR-2GT-LAN	Version
Order No.	<a href="#">1345270000</a>	Security/NAT/VPN/U-link Router, Gigabit Ethernet, 2 * RJ45
GTIN (EAN)	4050118149807	10/100/1000BaseT(X), IP20, -20 °C...70 °C
Qty.	1 ST	
Type	IE-SR-2GT-UMTS/3G	Version
Order No.	<a href="#">1345250000</a>	
GTIN (EAN)	4050118149715	
Qty.	1 ST	
Type	IE-SR-2GT-LTE/4G-EU	Version
Order No.	<a href="#">2535930000</a>	Security/NAT/VPN/U-link Router, with integrated multi-band modem (4G/3G/2G), EU-model, Gigabit Ethernet, 2x RJ45
GTIN (EAN)	4050118547603	10/100/1000BaseT(X), IP20, -20 °C...70 °C
Qty.	1 ST	
Type	IE-SR-2GT-LTE/4G-US	Version
Order No.	<a href="#">2535780000</a>	Security/NAT/VPN/U-link Router, with integrated multi-band modem (4G/3G/2G), US-model, Gigabit Ethernet, 2x RJ45
GTIN (EAN)	4050118547597	10/100/1000BaseT(X), IP20, -20 °C...70 °C
Qty.	1 ST	
Type	IE-SR-6GT-LAN	Version
Order No.	<a href="#">2535940000</a>	Security/NAT/VPN/U-link Router, Gigabit Ethernet, 6 * RJ45
GTIN (EAN)	4050118547610	10/100/1000BaseT(X), IP20, -20 °C...70 °C
Qty.	1 ST	
Type	IE-SR-6GT-LTE/4G-EU	Version
Order No.	<a href="#">2535960000</a>	Security/NAT/VPN/U-link Router, with integrated multi-band modem (4G/3G/2G), EU-model, Gigabit Ethernet, 6 * RJ45
GTIN (EAN)	4050118547634	10/100/1000BaseT(X), IP20, -20 °C...70 °C
Qty.	1 ST	
Type	IE-SR-6GT-LTE/4G-US	Version
Order No.	<a href="#">2535950000</a>	Security/NAT/VPN/U-link Router, with integrated multi-band modem (4G/3G/2G), US-model, Gigabit Ethernet, 6 * RJ45
GTIN (EAN)	4050118547627	10/100/1000BaseT(X), IP20, -20 °C...70 °C
Qty.	1 ST	