

**HDC XX5E01 FMSM12D-0050**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

Order No.	2451120050
Type	<a href="#">HDC XX5E01 FMSM12D-0050</a>
GTIN (EAN)	4050118521436
Qty.	1 items

**HDC XX5E01 FMSM12D-0050**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 11 g

**Temperatures**

Limit temperature -30 °C ... 90 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP 2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5

**General data**

Number of poles	4	Cable length	0.5 m
Coding	D-coded	Contact surface	Au (Gold)
Transmission rate	100 MBit/s	Insulation resistance	≥ 108 Ω
Category	Cat. 5e	Nominal voltage	250 V
Nominal current	4 A	Plugging cycles	≥ 100
Type	Female	Pollution severity	2
Opposite side version	Male, straight, M12D	Module side version	Female

**Cable technical specifications**

Cable length	0.5 m		
Sheathing colour	green		
Shielded	Yes		
Halogen	No, halogen-free		
Insulation	PE		
Sheath material	PUR		
Colour coding	white, yellow, blue, orange		
Outside diameter	Diameter	6.5 mm	
	Signs	±	
	Tolerance	0.2	
Outside diameter	6.5 mm ± 0.2		

**Classifications**

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-07
ECLASS 15.0	27-06-03-07		

**Drawings**

---

---

M12		M12
1	yellow	1
2	white	2
3	orange	3
4	blue	4

---

---

---