

**HDC XX6A01 MMSM12X-0500**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

Order No.	2451130500
Type	<a href="#">HDC XX6A01 MMSM12X-0500</a>
GTIN (EAN)	4050118508086
Qty.	1 items

## HDC XX6A01 MMSM12X-0500

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Net weight	465.62 g
------------	----------

## Temperatures

Limit temperature	-40 °C ... 90 °C
-------------------	------------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5

## General data

Number of poles	8	Cable length	5 m
Coding	X-coded	Contact surface	Au (Gold)
Transmission rate	10 Gbps, 10 Gbit/s	Insulation resistance	≥ 108 Ω
Category	Cat. 6A	Nominal voltage	50 V
Nominal current	0.5 A	Plugging cycles	≥ 2265 100
Type	Pin	Pollution severity	2
Opposite side version	Male, straight, M12X	Module side version	Male

## Cable technical specifications

Cable length	5 m	
Sheathing colour	blue	
Shielded	Yes	
Halogen	No	
Insulation	Expanded	
Sheath material	Radox EM 104	
Colour coding	white / orange, orange, white / green, green, white / brown, brown, white / blue, blue	
Outside diameter	Diameter	8.1 mm
	Signs	±
	Tolerance	0.5
Outside diameter	8.1 mm ± 0.5	

## Classifications

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-07
ECLASS 15.0	27-06-03-07		