

**HDC XX5E01 MFSXXX-3000****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

|            |                                        |
|------------|----------------------------------------|
| Order No.  | 2453553000                             |
| Type       | <a href="#">HDC XX5E01 MFSXXX-3000</a> |
| GTIN (EAN) | 4050118552539                          |
| Qty.       | 1 items                                |

## HDC XX5E01 MFSXXXX-3000

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |           |
|------------|-----------|
| Net weight | 1681.68 g |
|------------|-----------|

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5 |

## General data

|                     |            |                       |                  |
|---------------------|------------|-----------------------|------------------|
| Number of poles     | 4          | Cable length          | 30 m             |
| Coding              | D-coded    | Contact surface       | Au (Gold)        |
| Transmission rate   | 100 MBit/s | Insulation resistance | ≥ 108 Ω          |
| Category            | Cat. 5e    | Nominal voltage       | 250 V            |
| Nominal current     | 4 A        | Plugging cycles       | ≥ 100            |
| Pollution severity  | 2          | Opposite side version | Female, straight |
| Module side version | Male       |                       |                  |

## Cable technical specifications

|                  |                             |        |
|------------------|-----------------------------|--------|
| Cable length     | 30 m                        |        |
| Sheathing colour | green                       |        |
| Shielded         | Yes                         |        |
| Halogen          | No, halogen-free            |        |
| Insulation       | PE                          |        |
| Sheath material  | PUR                         |        |
| Colour coding    | white, yellow, blue, orange |        |
| Outside diameter | Diameter                    | 6.5 mm |
|                  | Signs                       | ±      |
|                  | Tolerance                   | 0.2    |
| Outside diameter | 6.5 mm ± 0.2                |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ETIM 10.0   | EC002599    | ECLASS 14.0 | 27-06-03-07 |
| ECLASS 15.0 | 27-06-03-07 |             |             |

**HDC XX5E01 MFSXXXX-3000**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

| M12 |        | M12 |
|-----|--------|-----|
| 1   | yellow | 1   |
| 2   | white  | 2   |
| 3   | orange | 3   |
| 4   | blue   | 4   |

