

EPG CUT 40

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Weidmüller is a specialist in the cutting of copper or aluminium cables. The range of products extends from cutting tools with direct force application for small cross-sections up to cutting tools for large diameters.

- Extremely fast processing thanks to two-stage hydraulic pump
- 360° revolving quick action crimping head
- Ergonomic handle and balanced weight distribution ensure fatigue-free and safe operation
- Permanent battery charge level control
- Monitoring of the working cycle and status display
- Error display in the event of malfunctions

General ordering data

Version	Cutting tools, Cutting tool
Order No.	2453830000
Type	EPG CUT 40
GTIN (EAN)	4050118468410
Qty.	1 items

EPG CUT 40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	70 mm	Depth (inches)	2.7559 inch
Height	365 mm	Height (inches)	14.3701 inch
Width	80 mm	Width (inches)	3.1496 inch
Net weight	3100 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Charging time	0.5 h	Version	Accumulator-hydraulic
Operating voltage	18 V		

Cutting tools

Copper cable - solid, max.	240 mm ²	Copper cable - stranded, max.	200 mm ²
Copper cable, max. diameter	40 mm	Charging time	0.5 h
Operating voltage	18 V	Single-core aluminium cable, max.(mm ²)	500 mm ²
Stranded aluminium cable, max (mm ²)	280 mm ²	Stranded aluminium cable, max. diameter	40 mm
Punching force	30 kN		

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		

Example of use

