

PRO COM CAN OPEN EX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Weidmüller's plug-in communication modules enable individual components to exchange relevant data with the cloud. This lays the foundation for targeted process optimization using condition monitoring and remote controllability - factors that play a decisive role in increasing efficiency, quality, process stability and availability can contribute. The communication modules are designed according to IP20 protected, can be operated without tools and can be flexibly adapted to different customisable communication protocols.

General ordering data

Version	Communication module
Order No.	2467340000
Type	PRO COM CAN OPEN EX
GTIN (EAN)	4050118481822
Qty.	1 items

PRO COM CAN OPEN EX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E258476
Certificate no. (cULusEX)	E470829

Dimensions and weights

Depth	33.6 mm	Depth (inches)	1.3228 inch
Height	74.4 mm	Height (inches)	2.9291 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	76 g		

Temperatures

Storage temperature	Operating temperature	-25 °C...70 °C
---------------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	1df9fee4-69cb-4b0a-a401-554c8cdbf60e

General data

Weight	36 g	
Protection degree	IP20	
MTTF	According to Standard	SN 29500
	Operating time (hours), min.	4082000 h
	Ambient temperature	40 °C
	Duty cycle	100 %

Classifications

ETIM 8.0	EC001604	ETIM 9.0	EC001604
ETIM 10.0	EC001604	ECLASS 14.0	27-24-26-08
ECLASS 15.0	27-24-26-08		