


**ES EPG/HPG 60 WM 6**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Version	Crimping tool insert, 6mm <sup>2</sup> , WM crimp
Order No.	<a href="#">2469380000</a>
Type	ES EPG/HPG 60 WM 6
GTIN (EAN)	4050118532937
Qty.	1 items

**ES EPG/HPG 60 WM 6**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Depth	22 mm	Depth (inches)	0.8661 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	150 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Crimp inserts**

Crimping width	7 mm	Crimp cross-section copper	6
Crimping width in mm	7		

**Description of contact**

Type of contact	Euro series cable lug	Conductor cross-section, max. AWG	10
Conductor cross-section, min. AWG	10	Crimping range, max.	6 mm <sup>2</sup>

**tool data crimping**

Crimping type/profile	WM crimp
Cable lug cross section	nominal 6 mm <sup>2</sup>

**Classifications**

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

**ES EPG/HPG 60 WM 6**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Tools**



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Type	EPG 60	Version
Order No.	<a href="#">2453810000</a>	Pressing tools, Tools, Pressing tool, 6mm <sup>2</sup> , 300mm <sup>2</sup> , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
GTIN (EAN)	4050118468434	
Qty.	1 ST	
Type	HPG 60	Version
Order No.	<a href="#">2453820000</a>	6mm <sup>2</sup> , 300mm <sup>2</sup> , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
GTIN (EAN)	4050118468427	
Qty.	1 ST	

**6 mm<sup>2</sup>**



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

Type	KRN-M4/-6	Version
Order No.	<a href="#">1497150000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118306767	
Qty.	100 ST	
Type	KRN-M5/-6	Version
Order No.	<a href="#">1497170000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118306590	
Qty.	100 ST	
Type	KRN-M6/-6	Version
Order No.	<a href="#">1497180000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118306729	
Qty.	100 ST	

## ES EPG/HPG 60 WM 6

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	KRN-M8/-6	Version
Order No.	<a href="#">1497190000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118306613	
Qty.	100 ST	
Type	KRN-M10/-6	Version
Order No.	<a href="#">1497200000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118306385	
Qty.	100 ST	
Type	KRN-M12/-6	Version
Order No.	<a href="#">1497210000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118306347	
Qty.	100 ST	
Type	KWN-M4/-6 90	Version
Order No.	<a href="#">1497220000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118306477	
Qty.	100 ST	
Type	KWN-M5/-6 90	Version
Order No.	<a href="#">1496120000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118305753	
Qty.	100 ST	
Type	KWN-M6/-6 90	Version
Order No.	<a href="#">1496130000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118305982	
Qty.	100 ST	
Type	KWN-M8/-6 90	Version
Order No.	<a href="#">1496140000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118306248	
Qty.	100 ST	
Type	KWN-M10/-6 90	Version
Order No.	<a href="#">1496150000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118305579	
Qty.	100 ST	
Type	KWN-M12/-6 90	Version
Order No.	<a href="#">1496170000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118305869	
Qty.	100 ST	
Type	VSTN/-6	Version
Order No.	<a href="#">1494720000</a>	cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> ,None
GTIN (EAN)	4050118304190	
Qty.	100 ST	
Type	KP-M5/-6	Version
Order No.	<a href="#">1497840000</a>	cable lug, terminal end,6 mm <sup>2</sup>
GTIN (EAN)	4050118307405	
Qty.	100 ST	
Type	KP-M6/-6	Version
Order No.	<a href="#">1497850000</a>	cable lug, terminal end,6 mm <sup>2</sup>
GTIN (EAN)	4050118307245	
Qty.	100 ST	
Type	KP-M8/-6	Version
Order No.	<a href="#">1497860000</a>	cable lug, terminal end,6 mm <sup>2</sup>
GTIN (EAN)	4050118307238	
Qty.	100 ST	

## ES EPG/HPG 60 WM 6

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	VPN/-6	Version	
Order No.	<a href="#">1498610000</a>		cable lug, terminal end,6 mm <sup>2</sup> ,6 mm <sup>2</sup> ,None
GTIN (EAN)	4050118307931		
Qty.	100 ST		