

## ES EPG/HPG 60 WM 25

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

### General ordering data

Version	Crimping tool insert, 25mm <sup>2</sup> , WM crimp
Order No.	<a href="#">2469560000</a>
Type	ES EPG/HPG 60 WM 25
GTIN (EAN)	4050118483840
Qty.	1 items

## ES EPG/HPG 60 WM 25

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	167 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Crimp inserts

Crimping width	12 mm	Crimp cross-section copper	25
Crimping width in mm	12		

## Description of contact

Type of contact	Euro series cable lug	Conductor cross-section, max. AWG	4
Conductor cross-section, min. AWG	4	Crimping range, max.	25 mm <sup>2</sup>

## tool data crimping

Crimping type/profile	WM crimp
Cable lug cross section	nominal 25 mm <sup>2</sup>

## Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		