

**ES EPG/HPG 60 WM 50**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Similar to illustration**

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

|            |  |
|------------|--|
| Version    | Crimping tool insert, 50mm <sup>2</sup> , WM crimp |
| Order No.  | <a href="#">2469580000</a>                         |
| Type       | ES EPG/HPG 60 WM 50                                |
| GTIN (EAN) | 4050118483864                                      |
| Qty.       | 1 items  |

**ES EPG/HPG 60 WM 50**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Depth      | 22 mm | Depth (inches)  | 0.8661 inch |
| Height     | 42 mm | Height (inches) | 1.6535 inch |
| Width      | 42 mm | Width (inches)  | 1.6535 inch |
| Net weight | 139 g |                 |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Crimp inserts**

|                      |      |                            |    |
|----------------------|------|----------------------------|----|
| Crimping width       | 5 mm | Crimp cross-section copper | 50 |
| Crimping width in mm | 5    |                            |    |

**Description of contact**

|                                   |                       |                                   |                    |
|-----------------------------------|-----------------------|-----------------------------------|--------------------|
| Type of contact                   | Euro series cable lug | Conductor cross-section, max. AWG | 1                  |
| Conductor cross-section, min. AWG | 1                     | Crimping range, max.              | 50 mm <sup>2</sup> |

**tool data crimping**

|                         |                            |
|-------------------------|----------------------------|
| Crimping type/profile   | WM crimp                   |
| Cable lug cross section | nominal 50 mm <sup>2</sup> |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001282    | ETIM 9.0    | EC001282    |
| ETIM 10.0   | EC001282    | ECLASS 14.0 | 21-04-90-90 |
| ECLASS 15.0 | 21-04-90-90 |             |             |