


ES EPG/HPG 60 WM 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	Crimping tool insert, 95mm ² , WM crimp
Order No.	2469600000
Type	ES EPG/HPG 60 WM 95
GTIN (EAN)	4050118483895
Qty.	1 items

ES EPG/HPG 60 WM 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	118.8 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Crimping width	5 mm	Crimp cross-section copper	95
Crimping width in mm	5		

Description of contact

Type of contact	Euro series cable lug	Conductor cross-section, max. AWG	3/0
Conductor cross-section, min. AWG	3/0	Crimping range, max.	95 mm ²

tool data crimping

Crimping type/profile	WM crimp
Cable lug cross section	nominal 95 mm ²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

ES EPG/HPG 60 WM 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	EPG 60	Version
Order No.	2453810000	Pressing tools, Tools, Pressing tool, 6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
GTIN (EAN)	4050118468434	
Qty.	1 ST	
Type	HPG 60	Version
Order No.	2453820000	6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
GTIN (EAN)	4050118468427	
Qty.	1 ST	

95 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M6/-95	Version
Order No.	1495820000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305531	
Qty.	25 ST	
Type	KRN-M8/-95	Version
Order No.	1495600000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305241	
Qty.	25 ST	
Type	KRN-M10/-95	Version
Order No.	1495610000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305371	
Qty.	25 ST	

ES EPG/HPG 60 WM 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KRN-M12/-95	Version
Order No.	1495620000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305265	
Qty.	25 ST	
Type	KRN-M14/-95	Version
Order No.	1495780000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305555	
Qty.	25 ST	
Type	KRN-M16/-95	Version
Order No.	1495630000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305326	
Qty.	25 ST	
Type	KRN-M20/-95	Version
Order No.	1495640000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305319	
Qty.	25 ST	
Type	KRN-M6/-95 S	Version
Order No.	1494430000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118303957	
Qty.	25 ST	
Type	KRN-M8/-95 S	Version
Order No.	1494890000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118304121	
Qty.	25 ST	
Type	KRN-M10/-95 S	Version
Order No.	1494900000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118304398	
Qty.	25 ST	
Type	KRN-M12/-95 S	Version
Order No.	1494910000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118304510	
Qty.	25 ST	
Type	KWN-M8/-95 90	Version
Order No.	1496080000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305685	
Qty.	25 ST	
Type	KWN-M10/-95 90	Version
Order No.	1496090000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305692	
Qty.	25 ST	
Type	KWN-M12/-95 90	Version
Order No.	1496100000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305487	
Qty.	25 ST	
Type	KWN-M14/-95 90	Version
Order No.	1494670000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118304411	
Qty.	25 ST	
Type	KWN-M16/-95 90	Version
Order No.	1496110000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305678	
Qty.	25 ST	

ES EPG/HPG 60 WM 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KWN-M8/-95 45	Version
Order No.	1496340000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305821	
Qty.	25 ST	
Type	KWN-M10/-95 45	Version
Order No.	1496350000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118306125	
Qty.	25 ST	
Type	KWN-M12/-95 45	Version
Order No.	1496370000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305890	
Qty.	25 ST	
Type	KWN-M16/-95 45	Version
Order No.	1496380000	cable lug, terminal end,95 mm ² ,95 mm ² - 95 mm ²
GTIN (EAN)	4050118305838	
Qty.	25 ST	
Type	VSTN/-95	Version
Order No.	1494770000	cable lug, terminal end,95 mm ² ,95 mm ² ,None
GTIN (EAN)	4050118304220	
Qty.	50 ST	
Type	KP-M8/-95	Version
Order No.	1498180000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307498	
Qty.	50 ST	
Type	KP-M10/-95	Version
Order No.	1498190000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307603	
Qty.	50 ST	
Type	KP-M12/-95	Version
Order No.	1498210000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307610	
Qty.	50 ST	
Type	KP-M14/-95	Version
Order No.	1498520000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307863	
Qty.	50 ST	
Type	KP-M16/-95	Version
Order No.	1498220000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307719	
Qty.	50 ST	
Type	KP-M20/-95	Version
Order No.	1498230000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307634	
Qty.	50 ST	
Type	KWPN-M8/-95 90	Version
Order No.	1497690000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307207	
Qty.	25 ST	
Type	KWPN-M10/-95 90	Version
Order No.	1497710000	cable lug, terminal end,95 mm ²
GTIN (EAN)	4050118307139	
Qty.	25 ST	

ES EPG/HPG 60 WM 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Accessories

Type	KWPN-M12/-95 90	Version
Order No.	1497720000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307214	
Qty.	25 ST	
Type	KWPN-M16/-95 90	Version
Order No.	1497730000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307054	
Qty.	25 ST	
Type	VPN/-95	Version
Order No.	1498680000	cable lug, terminal end,95 mm²,95 mm²,None
GTIN (EAN)	4050118307917	
Qty.	50 ST	
Type	KQN-M8/-95	Version
Order No.	1493260000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118303162	
Qty.	25 ST	
Type	KQN-M10/-95	Version
Order No.	1493270000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118303018	
Qty.	25 ST	
Type	KQN-M12/-95	Version
Order No.	1493280000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118302899	
Qty.	25 ST	
Type	KQN-M16/-95	Version
Order No.	1493290000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118303025	
Qty.	25 ST	
Type	KQN-M20/-95	Version
Order No.	1493310000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118303407	
Qty.	25 ST	
Type	KSN/-95	Version
Order No.	1492840000	cable lug, terminal end,95 mm²,95 mm²
GTIN (EAN)	4050118302790	
Qty.	25 ST	
Type	VPLN/-95	Version
Order No.	1492950000	cable lug, terminal end,95 mm²,95 mm²,None
GTIN (EAN)	4050118302622	
Qty.	50 ST	
Type	VSTN/95	Version
Order No.	1493090000	cable lug, terminal end,95 mm²,95 mm²,None
GTIN (EAN)	4050118302929	
Qty.	50 ST	

Accessories

120 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M8/-120	Version	
Order No.	1495790000		cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118305401		
Qty.	25 ST		
Type	KRN-M10/-120	Version	
Order No.	1495650000		cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118305289		
Qty.	25 ST		