


ES EPG/HPG 60 WM 120

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	Crimping tool insert, 120mm ² , WM crimp
Order No.	2469610000
Type	ES EPG/HPG 60 WM 120
GTIN (EAN)	4050118484007
Qty.	1 items

ES EPG/HPG 60 WM 120

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	134 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Crimping width	5 mm	Crimp cross-section copper	120
Crimping width in mm	5		

Description of contact

Type of contact	Euro series cable lug	Conductor cross-section, max. AWG	4/0
Conductor cross-section, min. AWG	4/0	Crimping range, max.	120 mm ²

tool data crimping

Crimping type/profile	WM crimp
Cable lug cross section	nominal 120 mm ²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

ES EPG/HPG 60 WM 120

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	EPG 60	Version
Order No.	2453810000	Pressing tools, Tools, Pressing tool, 6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
GTIN (EAN)	4050118468434	
Qty.	1 ST	
Type	HPG 60	Version
Order No.	2453820000	6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
GTIN (EAN)	4050118468427	
Qty.	1 ST	

120 mm²

120 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M8/-120	Version
Order No.	1495790000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118305401	
Qty.	25 ST	
Type	KRN-M10/-120	Version
Order No.	1495650000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118305289	
Qty.	25 ST	
Type	KRN-M12/-120	Version
Order No.	1495670000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118305258	
Qty.	25 ST	

ES EPG/HPG 60 WM 120

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KRN-M14/-120	Version
Order No.	1495800000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118305616	
Qty.	25 ST	
Type	KRN-M16/-120	Version
Order No.	1495680000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118305272	
Qty.	25 ST	
Type	KRN-M20/-120	Version
Order No.	1495690000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118305524	
Qty.	25 ST	
Type	KRN-M6/-120 S	Version
Order No.	1494410000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118304060	
Qty.	10 ST	
Type	KRN-M8/-120 S	Version
Order No.	1494420000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118304077	
Qty.	10 ST	
Type	KRN-M10/-120 S	Version
Order No.	1494920000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118304626	
Qty.	10 ST	
Type	KRN-M12/-120 S	Version
Order No.	1494930000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118304602	
Qty.	10 ST	
Type	KWN-M8/-120 90	Version
Order No.	1494680000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118304343	
Qty.	25 ST	
Type	KWN-M10/-120 90	Version
Order No.	1494450000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118304084	
Qty.	25 ST	
Type	KWN-M12/-120 90	Version
Order No.	1494470000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118304091	
Qty.	25 ST	
Type	KWN-M16/-120 90	Version
Order No.	1494480000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118304312	
Qty.	25 ST	
Type	KWN-M8/-120 45	Version
Order No.	1496390000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118305999	
Qty.	25 ST	
Type	KWN-M10/-120 45	Version
Order No.	1496400000	cable lug, terminal end, 120 mm ² , 120 mm ² - 120 mm ²
GTIN (EAN)	4050118306224	
Qty.	25 ST	

ES EPG/HPG 60 WM 120

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KWN-M12/-120 45	Version
Order No.	1496410000	cable lug, terminal end,120 mm ² ,120 mm ² - 120 mm ²
GTIN (EAN)	4050118306057	
Qty.	25 ST	
Type	KWN-M16/-120 45	Version
Order No.	1496420000	cable lug, terminal end,120 mm ² ,120 mm ² - 120 mm ²
GTIN (EAN)	4050118306118	
Qty.	25 ST	
Type	VSTN/-120	Version
Order No.	1494780000	cable lug, terminal end,120 mm ² ,120 mm ² ,None
GTIN (EAN)	4050118304282	
Qty.	25 ST	
Type	KP-M8/-120	Version
Order No.	1498480000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118307900	
Qty.	50 ST	
Type	KP-M10/-120	Version
Order No.	1498240000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118307368	
Qty.	50 ST	
Type	KP-M12/-120	Version
Order No.	1498250000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118307627	
Qty.	50 ST	
Type	KP-M14/-120	Version
Order No.	1498490000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118307771	
Qty.	50 ST	
Type	KP-M16/-120	Version
Order No.	1498270000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118307580	
Qty.	50 ST	
Type	KP-M20/-120	Version
Order No.	1498280000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118307702	
Qty.	50 ST	
Type	KWPN-M10/-120 90	Version
Order No.	1497750000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118307061	
Qty.	25 ST	
Type	KWPN-M12/-120 90	Version
Order No.	1497760000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118307184	
Qty.	25 ST	
Type	KWPN-M16/120 90	Version
Order No.	1497770000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118307030	
Qty.	25 ST	
Type	KWPN-M20/-120 90	Version
Order No.	1497780000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118307191	
Qty.	25 ST	

ES EPG/HPG 60 WM 120

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	VPN/-120	Version
Order No.	1498690000	cable lug, terminal end,120 mm ² ,120 mm ² ,None
GTIN (EAN)	4050118307795	
Qty.	25 ST	
Type	KQN-M8/-120	Version
Order No.	1493320000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118303186	
Qty.	25 ST	
Type	KQN-M10/-120	Version
Order No.	1493330000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118303070	
Qty.	25 ST	
Type	KQN-M12/-120	Version
Order No.	1493340000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118302998	
Qty.	25 ST	
Type	KQN-M16/-120	Version
Order No.	1493350000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118303100	
Qty.	25 ST	
Type	KQN-M20/-120	Version
Order No.	1493360000	cable lug, terminal end,120 mm ²
GTIN (EAN)	4050118303063	
Qty.	25 ST	
Type	VPLN/-120	Version
Order No.	1492960000	cable lug, terminal end,120 mm ² ,120 mm ² ,None
GTIN (EAN)	4050118302936	
Qty.	50 ST	
Type	VSTN/120	Version
Order No.	1493110000	cable lug, terminal end,120 mm ² ,120 mm ² ,None
GTIN (EAN)	4050118302813	
Qty.	50 ST	