

ES EPG/HPG 60 WM 150

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	Crimping tool insert, 150mm ² , WM crimp
Order No.	2469620000
Type	ES EPG/HPG 60 WM 150
GTIN (EAN)	405011848387 1
Qty.	1 items

ES EPG/HPG 60 WM 150

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	117.92 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Crimping width	5 mm	Crimp cross-section copper	150
Crimping width in mm	5		

Description of contact

Type of contact	Euro series cable lug	Conductor cross-section, max. AWG	5/0
Conductor cross-section, min. AWG	5/0	Crimping range, max.	150 mm ²

tool data crimping

Crimping type/profile	WM crimp
Cable lug cross section	nominal 150 mm ²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

ES EPG/HPG 60 WM 150

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	EPG 60	Version
Order No.	2453810000	Pressing tools, Tools, Pressing tool, 6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
GTIN (EAN)	4050118468434	
Qty.	1 ST	
Type	HPG 60	Version
Order No.	2453820000	6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
GTIN (EAN)	4050118468427	
Qty.	1 ST	

150 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M8/-150	Version
Order No.	1495700000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305333	
Qty.	25 ST	
Type	KRN-M10/-150	Version
Order No.	1495710000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305159	
Qty.	25 ST	
Type	KRN-M12/-150	Version
Order No.	1495720000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305296	
Qty.	25 ST	

ES EPG/HPG 60 WM 150

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KRN-M14/-150	Version
Order No.	1495810000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305500	
Qty.	25 ST	
Type	KRN-M16/-150	Version
Order No.	1495730000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305395	
Qty.	25 ST	
Type	KRN-M20/-150	Version
Order No.	1495740000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305357	
Qty.	25 ST	
Type	KRN-M6/-150 S	Version
Order No.	1494440000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118303964	
Qty.	10 ST	
Type	KRN-M8/-150 S	Version
Order No.	1494940000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304701	
Qty.	10 ST	
Type	KRN-M10/-150 S	Version
Order No.	1494950000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304473	
Qty.	10 ST	
Type	KRN-M12/-150 S	Version
Order No.	1494970000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304459	
Qty.	10 ST	
Type	KWN-M8/-150 90	Version
Order No.	1494490000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304107	
Qty.	25 ST	
Type	KWN-M10/150 90	Version
Order No.	1494500000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118303896	
Qty.	25 ST	
Type	KWN-M12/-150 90	Version
Order No.	1494510000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304305	
Qty.	25 ST	
Type	KWN-M16/-150 90	Version
Order No.	1494520000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118303995	
Qty.	25 ST	
Type	KWN-M20/-150 90	Version
Order No.	1494530000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304206	
Qty.	25 ST	
Type	KWN-M8/-150 45	Version
Order No.	1496430000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118306071	
Qty.	25 ST	

ES EPG/HPG 60 WM 150

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KWN-M10/-150 45	Version
Order No.	1496440000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305777	
Qty.	25 ST	
Type	KWN-M12/-150 45	Version
Order No.	1496450000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305906	
Qty.	25 ST	
Type	KWN-M16/-150 45	Version
Order No.	1496470000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118306132	
Qty.	25 ST	
Type	KWN-M20/-150 45	Version
Order No.	1496480000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305739	
Qty.	25 ST	
Type	VSTN/-150	Version
Order No.	1497380000	cable lug, terminal end, 150 mm ² , 150 mm ² , None
GTIN (EAN)	4050118306958	
Qty.	25 ST	
Type	KP-M8/-150	Version
Order No.	1498290000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307399	
Qty.	25 ST	

10 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KP-M10/-150	Version
Order No.	1498310000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307801	
Qty.	25 ST	

ES EPG/HPG 60 WM 150

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

150 mm²150 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KP-M12/-150	Version
Order No.	1498320000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307658	
Qty.	25 ST	
Type	KP-M14/-150	Version
Order No.	1498580000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118308112	
Qty.	25 ST	
Type	KP-M16/-150	Version
Order No.	1498330000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307641	
Qty.	25 ST	
Type	KP-M20/-150	Version
Order No.	1498340000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307740	
Qty.	25 ST	
Type	KWPN-M8/-150 90	Version
Order No.	1497790000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307085	
Qty.	25 ST	
Type	KWPN-M10/-150 90	Version
Order No.	1497810000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307221	
Qty.	25 ST	
Type	KWPN-M12/-150 90	Version
Order No.	1497820000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307306	
Qty.	25 ST	
Type	KWPN-M16/-150 90	Version
Order No.	1497830000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307160	
Qty.	25 ST	
Type	KWPN-M20/150 90	Version
Order No.	1496680000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118306088	
Qty.	25 ST	
Type	VPN/-150	Version
Order No.	1498710000	cable lug, terminal end, 150 mm ² , 150 mm ² , None
GTIN (EAN)	4050118308129	
Qty.	25 ST	

ES EPG/HPG 60 WM 150

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	VPLN/-150	Version	
Order No.	1492970000		cable lug, terminal end,150 mm ² ,150 mm ² ,None
GTIN (EAN)	4050118302912		
Qty.	50 ST		
Type	VSTN/150	Version	
Order No.	1493120000		cable lug, terminal end,150 mm ² ,150 mm ² ,None
GTIN (EAN)	4050118302905		
Qty.	50 ST		