

**MCB 489 2P B 3A ACDC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image****General ordering data**

Version	Miniature circuit breaker, Number of poles: 2, 3 A, white
Order No.	<a href="#">2477340000</a>
Type	MCB 489 2P B 3A ACDC
GTIN (EAN)	4050118492651
Qty.	6 items
Delivery status	This article will no longer be available in the future.
Available until	2025-09-01T00:00:00+02:00

## MCB 489 2P B 3A ACDC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	60.3 mm	Depth (inches)	2.374 inch
Height	116 mm	Height (inches)	4.5669 inch
Width	35.3 mm	Width (inches)	1.3898 inch
Net weight	166.5 g		

### Temperatures

Storage temperature		Ambient temperature	-35 °C...70 °C
Operating temperature		Humidity	40 °C / 95 % rel. humidity, no condensation

### Electrical data

Voltage type	AC/DC	Rated AC voltage	480277 V
Rated DC voltage	125 V	Nominal current	3 A
Interrupting capacity	10000.00 A		

### General data

Number of poles	2	Type of mounting	DIN rail
Type of fixing	Rail mounting	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Colour	white

### Classifications

ETIM 8.0	EC000042	ETIM 9.0	EC000042
ETIM 10.0	EC000042	ECLASS 14.0	27-14-19-01
ECLASS 15.0	27-14-19-01		