

MCB 489 3P B 32A ACDC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



General ordering data

Version	Miniature circuit breaker, Number of poles: 3, 32 A, white
Order No.	2477730000
Type	MCB 489 3P B 32A ACDC
GTIN (EAN)	4050118492262
Qty.	4 items
Delivery status	This article will no longer be available in the future.
Available until	2025-09-01T00:00:00+02:00

MCB 489 3P B 32A ACDC

Weidmüller Interface GmbH & Co. KG

 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	60.3 mm	Depth (inches)	2.374 inch
Height	116 mm	Height (inches)	4.5669 inch
Width	52.9 mm	Width (inches)	2.0827 inch
Net weight	249.75 g		

Temperatures

Storage temperature	Ambient temperature	-35 °C...70 °C
Operating temperature	Humidity	40 °C / 95 % rel. humidity, no condensation

Electrical data

Voltage type	AC/DC	Rated AC voltage	480277 V
Nominal current	32 A	Interrupting capacity	10000.00 A

General data

Number of poles	3	Type of mounting	DIN rail
Type of fixing	Rail mounting	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Colour	white

Classifications

ETIM 6.0	EC000042	ETIM 7.0	EC000042
ETIM 8.0	EC000042	ETIM 9.0	EC000042
ETIM 10.0	EC000042	ECLASS 9.0	27-14-19-01
ECLASS 9.1	27-14-19-01	ECLASS 10.0	27-14-19-01
ECLASS 11.0	27-14-19-01	ECLASS 12.0	27-14-19-01
ECLASS 13.0	27-14-19-01	ECLASS 14.0	27-14-19-01
ECLASS 15.0	27-14-19-01		