

MCB 489 1P C 10A ACDC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Miniature circuit breaker, Number of poles: 1, 10 A, white
Order No.	2477900000
Type	MCB 489 1P C 10A ACDC
GTIN (EAN)	4050118492095
Qty.	12 items
Delivery status	This article will no longer be available in the future.
Available until	2025-09-01T00:00:00+02:00

MCB 489 1P C 10A ACDC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	60.2 mm	Depth (inches)	2.3701 inch
Height	116 mm	Height (inches)	4.5669 inch
Width	17.6 mm	Width (inches)	0.6929 inch
Net weight	83.25 g		

Temperatures

Storage temperature	Ambient temperature	-35 °C...70 °C
Operating temperature	Humidity	40 °C / 95 % rel. humidity, no condensation

Electrical data

Voltage type	AC/DC	Rated AC voltage	277 V
Rated DC voltage	60 V	Nominal current	10 A
Interrupting capacity	10000.00 A		

General data

Number of poles	1	Type of mounting	DIN rail
Type of fixing	Rail mounting	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Colour	white

Classifications

ETIM 6.0	EC000042	ETIM 7.0	EC000042
ETIM 8.0	EC000042	ETIM 9.0	EC000042
ETIM 10.0	EC000042	ECLASS 9.0	27-14-19-01
ECLASS 9.1	27-14-19-01	ECLASS 10.0	27-14-19-01
ECLASS 11.0	27-14-19-01	ECLASS 12.0	27-14-19-01
ECLASS 13.0	27-14-19-01	ECLASS 14.0	27-14-19-01
ECLASS 15.0	27-14-19-01		