

MCB 489 2P C 6A ACDC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



General ordering data

Version	Miniature circuit breaker, Number of poles: 2, 6 A, white
Order No.	2478120000
Type	MCB 489 2P C 6A ACDC
GTIN (EAN)	4050118491876
Qty.	36 items
Delivery status	This article will no longer be available in the future.
Available until	2025-09-01T00:00:00+02:00

MCB 489 2P C 6A ACDC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	60.3 mm	Depth (inches)	2.374 inch
Height	116 mm	Height (inches)	4.5669 inch
Width	35.3 mm	Width (inches)	1.3898 inch
Net weight	27.75 g		

Temperatures

Storage temperature	Ambient temperature	-35 °C...70 °C
Operating temperature	Humidity	40 °C / 95 % rel. humidity, no condensation

Electrical data

Voltage type	AC/DC	Rated AC voltage	480/277 V
Rated DC voltage	125 V	Nominal current	6 A
Interrupting capacity	10000.00 A		

General data

Number of poles	2	Type of mounting	DIN rail
Type of fixing	Rail mounting	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Colour	white

Classifications

ETIM 8.0	EC000042	ETIM 9.0	EC000042
ETIM 10.0	EC000042	ECLASS 14.0	27-14-19-01
ECLASS 15.0	27-14-19-01		