

MCB 1077 1P B 4A ACDC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Miniature circuit breaker, Number of poles: 1, 4 A, white
Order No.	2479340000
Type	MCB 1077 1P B 4A ACDC
GTIN (EAN)	4050118490657
Qty.	12 items
Delivery status	This article will no longer be available in the future.
Available until	2025-09-01T00:00:00+02:00

MCB 1077 1P B 4A ACDC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	60.2 mm	Depth (inches)	2.3701 inch
Height	82 mm	Height (inches)	3.2283 inch
Width	17.6 mm	Width (inches)	0.6929 inch
Net weight	83.25 g		

Temperatures

Storage temperature	Ambient temperature	-35 °C...70 °C
Operating temperature	Humidity	40 °C / 95 % rel. humidity, no condensation

Electrical data

Voltage type	AC/DC	Rated AC voltage	277 V
Rated DC voltage	60 V	Nominal current	4 A
Interrupting capacity	10000.00 A		

General data

Number of poles	1	Type of mounting	DIN rail
Type of fixing	Rail mounting	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Colour	white

Classifications

ETIM 8.0	EC000042	ETIM 9.0	EC000042
ETIM 10.0	EC000042	ECLASS 14.0	27-14-19-01
ECLASS 15.0	27-14-19-01		