


**RKDG D18 WG PT6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Intelligent cabling solutions can save you valuable time and money.

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread

Integration of operating and signalling devices into the seal possible

**General ordering data**

Version	Field Power® sealing insert, Seal, IP54, with corresponding enclosure, EPDM
Order No.	<a href="#">2491870000</a>
Type	RKDG D18 WG PT6
GTIN (EAN)	4050118501537
Qty.	10 items

**RKDG D18 WG PT6**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	18 mm	Depth (inches)	0.7087 inch
Height	33.8 mm	Height (inches)	1.3307 inch
Width	46.7 mm	Width (inches)	1.8386 inch
Net weight	21.8 g		

**Temperatures**

Storage temperature -40 °C...85 °C      Operating temperature -40 °C...85 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Basic material	EPDM	Silicone	No
Colour	black	Design	Seal
Protection degree	IP54, with corresponding enclosure	UL 94 flammability rating	HB
Mounting position, installation notice	in FieldPower® sealing slot	Line type	round
Outer cable diameter, min.	18.5 mm	Outer cable diameter, max.	20.5 mm

**Classifications**

ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 14.0	27-18-28-15
ECLASS 15.0	27-18-28-15		