

RCL425024T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Similar to illustration

General ordering data

Version	, Relay, Number of contacts: 2, CO contact AgNi, Rated control voltage: 24 V DC $\pm 10\%$, Continuous current: 8 A, Plug-in connection
Order No.	2494270000
Type	RCL425024T
GTIN (EAN)	4050118517507
Qty.	20 items

RCL425024T

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	29 mm	Depth (inches)	1.1417 inch
Height	15.7 mm	Height (inches)	0.6181 inch
Width	12.7 mm	Width (inches)	0.5 inch
Net weight	13.3 g		

Temperatures

Storage temperature	Ambient temperature	-20 °C...70 °C
Operating temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Control side

Rated control voltage	24 V DC \pm 10 %	Status indicator	No
-----------------------	--------------------	------------------	----

Load side

Continuous current	8 A	Max. switching voltage, AC	250 V
Min. switching current	5 mA	Contact type	2 CO contact (AgNi)

Insulation coordination

Protection degree	IP40
-------------------	------

Connection data

Wire connection method	Plug-in connection
------------------------	--------------------

Classifications

ETIM 8.0	EC001437	ETIM 9.0	EC001437
ETIM 10.0	EC001437	ECLASS 14.0	27-37-16-01
ECLASS 15.0	27-37-16-01		