

**RCL425615T**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Similar to illustration

**General ordering data**

|            |   |
|------------|---|
| Version    | , Relay, Number of contacts: 2, CO contact AgNi, Rated control voltage: 115 V AC, Continuous current: 8 A, Plug-in connection |
| Order No.  | <a href="#">2494300000</a>  |
| Type       | RCL425615T  |
| GTIN (EAN) | 4050118517514   |
| Qty.       | 20 items  |

## RCL425615T

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 29 mm   | Depth (inches)  | 1.1417 inch |
| Height     | 15.7 mm | Height (inches) | 0.6181 inch |
| Width      | 12.7 mm | Width (inches)  | 0.5 inch    |
| Net weight | 13 g    |                 |             |

### Temperatures

|                       |                     |                |
|-----------------------|---------------------|----------------|
| Storage temperature   | Ambient temperature | -40 °C...70 °C |
| Operating temperature |                     |                |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Control side

|                       |          |                  |    |
|-----------------------|----------|------------------|----|
| Rated control voltage | 115 V AC | Status indicator | No |
|-----------------------|----------|------------------|----|

### Load side

|                         |                     |                            |       |
|-------------------------|---------------------|----------------------------|-------|
| Rated switching voltage | 250 V AC            | Max. switching voltage, AC | 132 V |
| Contact type            | 2 CO contact (AgNi) |                            |       |

### General data

|        |             |
|--------|-------------|
| Colour | Transparent |
|--------|-------------|

### Insulation coordination

|                    |   |                   |      |
|--------------------|---|-------------------|------|
| Pollution severity | 3 | Protection degree | IP67 |
|--------------------|---|-------------------|------|

### Connection data

|                        |                    |
|------------------------|--------------------|
| Wire connection method | Plug-in connection |
|------------------------|--------------------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001437    | ETIM 9.0    | EC001437    |
| ETIM 10.0   | EC001437    | ECLASS 14.0 | 27-37-16-01 |
| ECLASS 15.0 | 27-37-16-01 |             |             |