

**RCL425615T**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

Similar to illustration

**General ordering data**

Version	, Relay, Number of contacts: 2, CO contact AgNi gold-plated, Rated control voltage: 115 V AC, Continuous current: 8 A, Plug-in connection
Order No.	<a href="#">2494300000</a>
Type	RCL425615T
GTIN (EAN)	4050118517514
Qty.	20 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	29 mm	Depth (inches)	1.1417 inch
Height	15.7 mm	Height (inches)	0.6181 inch
Width	12.7 mm	Width (inches)	0.5 inch
Net weight	13 g		

**Temperatures**

Storage temperature	Ambient temperature	-40 °C...70 °C
Operating temperature		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Control side**

Rated control voltage	115 V AC	Status indicator	No
-----------------------	----------	------------------	----

**Load side**

Rated switching voltage	250 V AC	Max. switching voltage, AC	132 V
Contact type	2 CO contact (AgNi gold-plated)		

**General data**

Colour	Transparent
--------	-------------

**Insulation coordination**

Pollution severity	3	Protection degree	IP67
--------------------	---	-------------------	------

**Connection data**

Wire connection method	Plug-in connection
------------------------	--------------------

**Classifications**

ETIM 8.0	EC001437	ETIM 9.0	EC001437
ETIM 10.0	EC001437	ECLASS 14.0	27-37-16-01
ECLASS 15.0	27-37-16-01		