

**ESG 6/17 MM WS VPE1000**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Guaranteed long service life: ESG**

The multi-colour and multi-format labels have a strong adhesive layer to ensure the best possible adhesion to the underlying surface. Double laminated polyester makes the basic material very thin and yet extremely tear-resistant.

**Your benefits with MultiMark**

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

Version	ESG, Device markers, 6 x 17 mm, white
Order No.	<a href="#">2496790000</a>
Type	ESG 6/17 MM WS VPE1000
GTIN (EAN)	4050118506495
Qty.	1000 items

## ESG 6/17 MM WS VPE1000

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.1 mm	Depth (inches)	0.0039 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	0.01 g		

## Temperatures

Operating temperature range	-40...120 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Adhesive	Acrylate adhesive	
Version	Self-adhesive, halogen-free	
Width	17 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	120 °C	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	No	
Basic material	Polyester	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
	Number of markers per combination	1000
Approval acc. to UL 969	Yes	
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	
Number of markers per combination	1 Label reel = 1000 Device markers	
Operating temperature range	-40...120 °C	
Number per roll	1000	

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**Drawings**



## ESG 6/17 MM WS VPE1000

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

Type	RIBBON MM 76/360 SW	Version	
Order No.	<a href="#">2005080000</a>	Ink ribbon	
GTIN (EAN)	4050118389951		
Qty.	1 ST		

### THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

Type	MULTIMARK ROLLER 115	Version	
Order No.	<a href="#">1357420000</a>		
GTIN (EAN)	4050118160314		
Qty.	1 ST		

### THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version	
Order No.	<a href="#">2672590000</a>		
GTIN (EAN)	4050118708097		
Qty.	1 ST		