

ESG 8/20 MM WS VPE1000

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**Guaranteed long service life: ESG**

The multi-colour and multi-format labels have a strong adhesive layer to ensure the best possible adhesion to the underlying surface. Double laminated polyester makes the basic material very thin and yet extremely tear-resistant.

Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

| | |
|------------|---------------------------------------|
| Version | ESG, Device markers, 8 x 20 mm, white |
| Order No. | 2496810000 |
| Type | ESG 8/20 MM WS VPE1000 |
| GTIN (EAN) | 4050118508314 |
| Qty. | 1000 items |

ESG 8/20 MM WS VPE1000

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.1 mm | Depth (inches) | 0.0039 inch |
| Height | 8 mm | Height (inches) | 0.315 inch |
| Width | 20 mm | Width (inches) | 0.7874 inch |
| Net weight | 0.04 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...120 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|-------------------|-----------------------------------|--|
| Adhesive | Acrylate adhesive | Version | Self-adhesive, halogen-free |
| Width | 20 mm | UL 94 flammability rating | V-0 |
| Operating temperature range, max. | 120 °C | Operating temperature range, min. | -40 °C |
| Colour | white | Halogen | No |
| Basic material | Polyester | Printed characters | without |
| Approval acc. to UL 969 | Yes | compatible printer | THM MULTIMARK , THM MULTIMARK PLUS |
| Operating temperature range | -40...120 °C | Number per roll | 1000 |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings

