


ES EPG/HPG 60 HEX 25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	Crimping tool insert, 25mm ² , Hexagonal crimp
Order No.	2505180000
Type	ES EPG/HPG 60 HEX 25
GTIN (EAN)	4050118519570
Qty.	1 items

ES EPG/HPG 60 HEX 25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	167 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Identification number	10	Crimping width	5 mm
Crimp cross-section aluminium	10	Crimp cross-section copper	25
Crimping width in mm	12		

Description of contact

Type of contact	DIN 46235 cable lug, DIN 46267 Part 1 cable lug	Conductor cross-section, max. AWG	4
Conductor cross-section, min. AWG	4	Crimping range, max.	25 mm ²

tool data crimping

Crimping type/profile	Hexagonal crimp
Cable lug cross section	nominal 25 mm ²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

ES EPG/HPG 60 HEX 25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	EPG 60	Version
Order No.	2453810000	Pressing tools, Tools, Pressing tool, 6mm ² , 300mm ² , Hexagonal
GTIN (EAN)	4050118468434	crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
Qty.	1 ST	
Type	HPG 60	Version
Order No.	2453820000	6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp,
GTIN (EAN)	4050118468427	Trapezoidal crimp, Oval crimping
Qty.	1 ST	

25 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M5/-25	Version
Order No.	1495830000	cable lug, terminal end, 25 mm ² , 25 mm ² - 25 mm ²
GTIN (EAN)	4050118305562	
Qty.	100 ST	
Type	KRN-M6/-25	Version
Order No.	1496490000	cable lug, terminal end, 25 mm ² , 25 mm ² - 25 mm ²
GTIN (EAN)	4050118305784	
Qty.	100 ST	
Type	KRN-M8/-25	Version
Order No.	1496500000	cable lug, terminal end, 25 mm ² , 25 mm ² - 25 mm ²
GTIN (EAN)	4050118305975	
Qty.	100 ST	

ES EPG/HPG 60 HEX 25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	KRN-M10/-25	Version
Order No.	1496510000	cable lug, terminal end, 25 mm², 25 mm² - 25 mm²
GTIN (EAN)	4050118305814	
Qty.	100 ST	
Type	KRN-M12/-25	Version
Order No.	1496520000	cable lug, terminal end, 25 mm², 25 mm² - 25 mm²
GTIN (EAN)	4050118306163	
Qty.	100 ST	
Type	KRN-M14/-25	Version
Order No.	1496530000	cable lug, terminal end, 25 mm², 25 mm² - 25 mm²
GTIN (EAN)	4050118305883	
Qty.	100 ST	
Type	KWN-M6/-25 90	Version
Order No.	1495850000	cable lug, terminal end, 25 mm², 25 mm² - 25 mm²
GTIN (EAN)	4050118305456	
Qty.	100 ST	
Type	KWN-M8/-25 90	Version
Order No.	1495870000	cable lug, terminal end, 25 mm², 25 mm² - 25 mm²
GTIN (EAN)	4050118305470	
Qty.	100 ST	
Type	KWN-M10/-25 90	Version
Order No.	1495880000	cable lug, terminal end, 25 mm², 25 mm² - 25 mm²
GTIN (EAN)	4050118305449	
Qty.	100 ST	
Type	KWN-M12/-25 90	Version
Order No.	1495890000	cable lug, terminal end, 25 mm², 25 mm² - 25 mm²
GTIN (EAN)	4050118305647	
Qty.	100 ST	
Type	KWN-M14/-25 90	Version
Order No.	1495900000	cable lug, terminal end, 25 mm², 25 mm² - 25 mm²
GTIN (EAN)	4050118305517	
Qty.	100 ST	

240 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KWN-M6/-25 45	Version
Order No.	1496180000	cable lug, terminal end, 25 mm², 25 mm² - 25 mm²
GTIN (EAN)	4050118305876	
Qty.	100 ST	

ES EPG/HPG 60 HEX 25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	KWN-M8/-25 45	Version
Order No.	1496190000	cable lug, terminal end, 25 mm ² , 25 mm ² - 25 mm ²
GTIN (EAN)	4050118306231	
Qty.	100 ST	
Type	KWN-M10/-25 45	Version
Order No.	1496200000	cable lug, terminal end, 25 mm ² , 25 mm ² - 25 mm ²
GTIN (EAN)	4050118305593	
Qty.	100 ST	
Type	KWN-M12/-25 45	Version
Order No.	1496210000	cable lug, terminal end, 25 mm ² , 25 mm ² - 25 mm ²
GTIN (EAN)	4050118305715	
Qty.	100 ST	

25 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	VSTN/-25	Version
Order No.	1494730000	cable lug, terminal end, 25 mm ² , 25 mm ² , None
GTIN (EAN)	4050118304275	
Qty.	50 ST	
Type	KP-M6/-25	Version
Order No.	1497970000	cable lug, terminal end, 25 mm ²
GTIN (EAN)	4050118307412	
Qty.	100 ST	
Type	KP-M8/-25	Version
Order No.	1497980000	cable lug, terminal end, 25 mm ²
GTIN (EAN)	4050118307528	
Qty.	100 ST	
Type	KP-M10/-25	Version
Order No.	1497990000	cable lug, terminal end, 25 mm ²
GTIN (EAN)	4050118307535	
Qty.	100 ST	
Type	KP-M12/-25	Version
Order No.	1498000000	cable lug, terminal end, 25 mm ²
GTIN (EAN)	4050118307504	
Qty.	100 ST	
Type	KP-M16/-25	Version
Order No.	1498010000	cable lug, terminal end, 25 mm ²
GTIN (EAN)	4050118307443	
Qty.	100 ST	

ES EPG/HPG 60 HEX 25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	KWPN-M6/-25 90	Version
Order No.	1497490000	cable lug, terminal end,25 mm²
GTIN (EAN)	4050118306668	
Qty.	100 ST	
Type	KWPN-M8/-25 90	Version
Order No.	1497510000	cable lug, terminal end,25 mm²
GTIN (EAN)	4050118306972	
Qty.	100 ST	
Type	KWPN-M10/-25 90	Version
Order No.	1497520000	cable lug, terminal end,25 mm²
GTIN (EAN)	4050118306989	
Qty.	100 ST	
Type	KWPN-M12/-25 90	Version
Order No.	1497530000	cable lug, terminal end,25 mm²
GTIN (EAN)	4050118307108	
Qty.	100 ST	
Type	VPN/-25	Version
Order No.	1498640000	cable lug, terminal end,25 mm²,25 mm²,None
GTIN (EAN)	4050118308013	
Qty.	100 ST	
Type	KQN-M5/-25	Version
Order No.	1494120000	cable lug, terminal end,25 mm²
GTIN (EAN)	4050118303827	
Qty.	50 ST	
Type	KQN-M6/-25	Version
Order No.	1494130000	cable lug, terminal end,25 mm²
GTIN (EAN)	4050118303858	
Qty.	50 ST	
Type	KQN-M8/-25	Version
Order No.	1494140000	cable lug, terminal end,25 mm²
GTIN (EAN)	4050118303872	
Qty.	50 ST	
Type	KQN-M10/-25	Version
Order No.	1494150000	cable lug, terminal end,25 mm²
GTIN (EAN)	4050118303865	
Qty.	50 ST	
Type	KQN-M12/-25	Version
Order No.	1494160000	cable lug, terminal end,25 mm²
GTIN (EAN)	4050118303902	
Qty.	50 ST	
Type	KQN-M16/-25	Version
Order No.	1493490000	cable lug, terminal end,25 mm²
GTIN (EAN)	4050118303148	
Qty.	50 ST	
Type	KSN/-25	Version
Order No.	1492800000	cable lug, terminal end,25 mm²,25 mm²
GTIN (EAN)	4050118302592	
Qty.	50 ST	
Type	VPLN/-25	Version
Order No.	1492910000	cable lug, terminal end,25 mm²,25 mm²,None
GTIN (EAN)	4050118302646	
Qty.	100 ST	

ES EPG/HPG 60 HEX 25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	VSTN/25	Version	
Order No.	1493050000	cable lug, terminal end,25 mm²,25 mm²,None	
GTIN (EAN)	4050118302783		
Qty.	100 ST		