

ES EPG/HPG 60 HEX 70

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	Crimping tool insert, 70mm ² , Hexagonal crimp
Order No.	2505210000
Type	ES EPG/HPG 60 HEX 70
GTIN (EAN)	4050118519594
Qty.	1 items

ES EPG/HPG 60 HEX 70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	119.68 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Identification number	16	Crimping width	5 mm
Crimp cross-section aluminium	50	Crimp cross-section copper	70
Crimping width in mm	5		

Description of contact

Type of contact	DIN 46235 cable lug, DIN 46267 Part 1 cable lug	Conductor cross-section, max. AWG	2/0
Conductor cross-section, min. AWG	2/0	Crimping range, max.	70 mm ²

tool data crimping

Crimping type/profile	Hexagonal crimp
Cable lug cross section	nominal 70 mm ²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

ES EPG/HPG 60 HEX 70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	EPG 60	Version
Order No.	2453810000	Pressing tools, Tools, Pressing tool, 6mm ² , 300mm ² , Hexagonal
GTIN (EAN)	4050118468434	crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
Qty.	1 ST	
Type	HPG 60	Version
Order No.	2453820000	6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp,
GTIN (EAN)	4050118468427	Trapezoidal crimp, Oval crimping
Qty.	1 ST	

70 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M6/-70	Version
Order No.	1496640000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305951	
Qty.	25 ST	
Type	KRN-M8/-70	Version
Order No.	1496650000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305791	
Qty.	25 ST	
Type	KRN-M10/-70	Version
Order No.	1496670000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305845	
Qty.	25 ST	

ES EPG/HPG 60 HEX 70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KRN-M12/-70	Version
Order No.	1495570000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304992	
Qty.	25 ST	
Type	KRN-M14/-70	Version
Order No.	1495770000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305166	
Qty.	25 ST	
Type	KRN-M16/-70	Version
Order No.	1495580000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305340	
Qty.	25 ST	
Type	KRN-M20/-70	Version
Order No.	1495590000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305302	
Qty.	25 ST	
Type	KRN-M6/-70 S	Version
Order No.	1494850000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304152	
Qty.	25 ST	
Type	KRN-M8/-70 S	Version
Order No.	1494860000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304527	
Qty.	25 ST	
Type	KRN-M10/-70 S	Version
Order No.	1494870000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304503	
Qty.	25 ST	
Type	KRN-M12/-70 S	Version
Order No.	1494880000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304435	
Qty.	25 ST	
Type	KWN-M6/-70 90	Version
Order No.	1496010000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305609	
Qty.	25 ST	
Type	KWN-M8/-70 90	Version
Order No.	1496020000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305180	
Qty.	25 ST	
Type	KWN-M10/-70 90	Version
Order No.	1496030000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305432	
Qty.	25 ST	
Type	KWN-M12/-70 90	Version
Order No.	1496040000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305463	
Qty.	25 ST	
Type	KWN-M14/-70 90	Version
Order No.	1494660000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304183	
Qty.	25 ST	

ES EPG/HPG 60 HEX 70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KWN-M16/-70 90	Version
Order No.	1496050000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305708	
Qty.	25 ST	
Type	KWN-M20/-70 90	Version
Order No.	1496070000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305661	
Qty.	25 ST	
Type	KWN-M8/-70 45	Version
Order No.	1496310000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305944	
Qty.	25 ST	
Type	KWN-M10/-70 45	Version
Order No.	1496320000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118306255	
Qty.	25 ST	
Type	KWN-M12/-70 45	Version
Order No.	1496330000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305586	
Qty.	25 ST	
Type	VSTN/-70	Version
Order No.	1494760000	cable lug, terminal end,70 mm ² ,70 mm ² ,None
GTIN (EAN)	4050118304299	
Qty.	50 ST	
Type	KP-M8/-70	Version
Order No.	1498130000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307351	
Qty.	50 ST	
Type	KP-M10/-70	Version
Order No.	1498140000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307429	
Qty.	50 ST	
Type	KP-M12/-70	Version
Order No.	1498150000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307467	
Qty.	50 ST	
Type	KP-M14/-70	Version
Order No.	1498560000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307696	
Qty.	50 ST	
Type	KP-M16/-70	Version
Order No.	1498160000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307481	
Qty.	50 ST	
Type	KP-M20/-70	Version
Order No.	1498170000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307344	
Qty.	50 ST	
Type	KWPN-M8/-70 90	Version
Order No.	1497640000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307047	
Qty.	25 ST	

ES EPG/HPG 60 HEX 70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KWPN-M10/-70 90	Version
Order No.	1497650000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307177	
Qty.	25 ST	
Type	KWPN-M12/-70 90	Version
Order No.	1497660000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307092	
Qty.	25 ST	
Type	KWPN-M16/-70 90	Version
Order No.	1497680000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307122	
Qty.	25 ST	
Type	VPN/-70	Version
Order No.	1498670000	cable lug, terminal end,70 mm ² ,70 mm ² ,None
GTIN (EAN)	4050118308020	
Qty.	50 ST	
Type	KQN-M6/-70	Version
Order No.	1493190000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118303261	
Qty.	50 ST	
Type	KQN-M8/-70	Version
Order No.	1493210000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118302875	
Qty.	50 ST	
Type	KQN-M10/-70	Version
Order No.	1493220000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118302882	
Qty.	50 ST	
Type	KQN-M12/-70	Version
Order No.	1493230000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118303032	
Qty.	50 ST	
Type	KQN-M16/-70	Version
Order No.	1493240000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118303131	
Qty.	50 ST	
Type	KQN-M20/-70	Version
Order No.	1493250000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118303087	
Qty.	50 ST	
Type	KSN/-70	Version
Order No.	1492830000	cable lug, terminal end,70 mm ² ,70 mm ²
GTIN (EAN)	4050118302585	
Qty.	50 ST	
Type	VPLN/-70	Version
Order No.	1492940000	cable lug, terminal end,70 mm ² ,70 mm ² ,None
GTIN (EAN)	4050118302738	
Qty.	100 ST	
Type	VSTN/70	Version
Order No.	1493080000	cable lug, terminal end,70 mm ² ,70 mm ² ,None
GTIN (EAN)	4050118302967	
Qty.	50 ST	