

ES EPG 60/HPG DIN 25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	Crimping tool insert, 25mm ² , Indent crimp
Order No.	2505310000
Type	ES EPG 60/HPG DIN 25
GTIN (EAN)	4050118519693
Qty.	1 items

ES EPG 60/HPG DIN 25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	2 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Crimping width	10 mm	Crimp cross-section copper	25
Crimping width in mm	10		

Description of contact

Type of contact	DIN 46234 cable lug, DIN 46341 Part 1 cable lug, DIN 46230 cable lug	Conductor cross-section, max. AWG	4
Conductor cross-section, min. AWG	4	Crimping range, max.	25 mm ²

tool data crimping

Crimping type/profile	Indent crimp
Cable lug cross section	nominal 25 mm ²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		