

WB I SK 4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

Version	Screwdriver insert
Order No.	2506070000
Type	WB I SK 4
GTIN (EAN)	4050118520521
Qty.	1 items
Packaging	miscellaneous

Technical data

Dimensions and weights

Depth	7 mm	Depth (inches)	0.2756 inch
Height	75 mm	Height (inches)	2.9527 inch
Width	7 mm	Width (inches)	0.2756 inch
Net weight	10 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE insulated interchangeable blade for hexagonal head screws
------------------------	---

Screwing tools

Form	Hexagon / Allen key	Size	4
Torque setting, max.	5.5 Nm		

Classifications

ETIM 6.0	EC002120	ETIM 7.0	EC002120
ETIM 8.0	EC002120	ETIM 9.0	EC002120
ETIM 10.0	EC002120	ECLASS 9.0	21-04-92-19
ECLASS 9.1	21-04-04-90	ECLASS 10.0	21-04-92-19
ECLASS 11.0	21-04-04-35	ECLASS 12.0	21-04-04-35
ECLASS 13.0	21-04-04-35	ECLASS 14.0	21-04-04-35
ECLASS 15.0	21-04-04-35		