

UR67-MP-HP-16DIO-12-60M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Similar to illustration

More performance. Simplified.

u-remote.

Weidmüller u-remote – our innovative remote I/O concept with IP 67 which focuses purely on user benefits: tailored planning, faster installation, safer start-up, no more downtime. For considerably improved performance and greater productivity. u-remote stands for "More Performance". Simplified

General ordering data

Version	Automation Products - u-remote IP67
Order No.	2512840000
Type	UR67-MP-HP-16DIO-12-60M
GTIN (EAN)	4050118527797
Qty.	1 items

UR67-MP-HP-16DIO-12-60M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Dimensions and weights

Height	17.6 mm	Height (inches)	0.6929 inch
Width	59.6 mm	Width (inches)	2.3465 inch
Net weight	500 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	82327f13-cd27-455a-ab5b-a62e1996dcf8

Digital inputs

Diagnostic display	Per channel, via LED, red	
Status indicator	Per channel, via LED, yellow	
Digital inputs	Short-circuit protection	Yes
	Overload protection	Yes
	Reverse polarity protection	Yes

Digital outputs

Diagnostic display	Per channel, via LED, red	
Digital outputs	Short-circuit protection	Yes
	Overload protection	Yes
	Reverse polarity protection	Yes
Short-circuit proof	Yes	
Output voltage, low	min. (UL -1)	
Status indicator	Per channel, via LED, yellow	
Output voltage, high	max. 2 V	

General data

UL 94 flammability rating	UL 94	Protection degree	IP67
---------------------------	-------	-------------------	------

Supply voltage

Power consumption of module electronics	100 mA typical
---	----------------

Classifications

ETIM 8.0	EC001599	ETIM 9.0	EC001599
ETIM 10.0	EC001599	ECLASS 14.0	27-24-26-04
ECLASS 15.0	27-24-26-04		