


THM VIN DIA 12.5 GN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Customised identification: EL

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the height can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

General ordering data

Version	THM, Device markers, green
Order No.	2517950000
Type	THM VIN DIA 12.5 GN
GTIN (EAN)	4050118530162
Qty.	4200 items

THM VIN DIA 12.5 GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Diameter	12.5 mm	Net weight	0.04 g

Temperatures

Storage temperature	23	Operating temperature range	-30...90 °C
---------------------	----	-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive		
Number per sheet	1		
Printing method	Thermal transfer		
Version	Endless, Self-adhesive		
UL 94 flammability rating	HB		
Operating temperature range, max.	90 °C		
Operating temperature range, min.	-30 °C		
Colour	green		
Halogen	Yes		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Approval acc. to UL 969	No		
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Device markers		
Operating temperature range	-30...90 °C		
Number per roll	1		

Device markers

Diameter	12.5 mm	Halogen	Yes
----------	---------	---------	-----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

THM VIN DIA 12.5 GN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	2005070000	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		