



- supplied loose in polybag
- Weidmüller colour code

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 10 mm, 8 mm, Turquoise |
| Order No. | 2525 190000 |
| Type | H0,34/12S TK |
| GTIN (EAN) | 4050118536843 |
| Qty. | 500 items |

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 125 mm | Height (inches) | 4.9212 inch |
| Net weight | 0.05 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

Version Standard

Wire-end ferrules

| | | | |
|---|----------------------|------------------|----------|
| Contact surface length (L2) | 8 mm | L1 in mm | 12.00 mm |
| Wire connection cross section AWG, max. | AWG 22 | Stripping length | 10 mm |
| Conductor cross-section | 0.34 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ETIM 10.0 | EC000005 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 | | |