

EL 12 MM GN 30M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Customised identification: EL

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the height can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

| | |
|------------|-----------------------------------|
| Version | THM, Device markers, 12 x , green |
| Order No. | 2528320000 |
| Type | EL 12 MM GN 30M |
| GTIN (EAN) | 4050118539219 |
| Qty. | 1 items |

EL 12 MM GN 30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 0.1 mm | Depth (inches) | 0.0039 inch |
| Height | 12 mm | Height (inches) | 0.4724 inch |
| Length | 30000 mm | Length (inches) | 1181.1 inch |
| Net weight | 107 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...120 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|-------------------|-----------------------------------|--|
| Adhesive | Acrylate adhesive | Version | halogen-free, Self-adhesive |
| UL 94 flammability rating | V-0 | Operating temperature range, max. | 120 °C |
| Operating temperature range, min. | -40 °C | Colour | green |
| Halogen | No | Length | 30000 mm |
| Basic material | Polyester | Printed characters | without |
| Approval acc. to UL 969 | Yes | compatible printer | THM MULTIMARK , THM MULTIMARK PLUS |
| Operating temperature range | -40...120 °C | Number per roll | 1 |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings

