

## H0,5/14DS W BD GSP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

### Similar to illustration



- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code

### General ordering data

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Standard, 10 mm, 8 mm, white |
| Order No.  | <a href="#">2528590000</a>                     |
| Type       | H0,5/14DS W BD GSP                             |
| GTIN (EAN) | 4050118539097                                  |
| Qty.       | 4200 items                                     |

**H0,5/14DS W BD GSP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



|                       |                            |
|-----------------------|----------------------------|
| ROHS                  | Conform                    |
| UL File Number Search | <a href="#">UL Website</a> |
| Certificate No. (UR)  | E354986                    |

**Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 0.07 g |
|------------|--------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Technical data**

|                        |                                  |         |          |
|------------------------|----------------------------------|---------|----------|
| Description of article | Wire end ferrules on reel, white | Version | Standard |
|------------------------|----------------------------------|---------|----------|

**Wire-end ferrules**

|                               |                     |   |         |
|-------------------------------|---------------------|---|---------|
| Contact surface diameter (D1) | 1 mm                | Contact surface length (L2)             | 8 mm    |
| Collar diameter (D2)          | 2.9 mm              | Plastic collar thickness (S2)           | 0.25 mm |
| L1 in mm                      | 14.00 mm            | Wire connection cross section AWG, max. | AWG 20  |
| Metal sleeve thickness (S1)   | 0.15 mm             | Stripping length                        | 10 mm   |
| Conductor cross-section       | 0.5 mm <sup>2</sup> | Colour code                             | DIN     |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ETIM 10.0   | EC000005    | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 |             |             |

Drawing

