

WIL-BM-SK-M12-3.0U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Motion detector for the WIL-LED luminaire with screw connection, 3m supply cable and M12 cable for connection to the WIL lamp. Switching time adjustable.

General ordering data

Order No.	2537700000
Type	WIL-BM-SK-M12-3.0U
GTIN (EAN)	4050118549140
Qty.	1 items

WIL-BM-SK-M12-3.0U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	44 mm	Depth (inches)	1.7323 inch
Height	33 mm	Height (inches)	1.2992 inch
Width	76 mm	Width (inches)	2.9921 inch
Net weight	100 g		

Temperatures

Operating temperature -20 - 60°C

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	82a8bf14-9104-4ca4-ab0c-226d976fdcac

Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Cable length	3 m	Core cross-section	0.34 mm ²

Connection data

Coding	A	Connection thread	M12
Tightening torque	0.8 Nm	Wiring	PIN 4: + (black), PIN 3: - (blue)

Electric data

Rated voltage 24 V DC Rated current < 6.0 A

General technical data

Protection degree	IP20		
Dwell time, min.	1 min		
Dwell time, max.	10 min		
Detection range	min.	0 m	
	max.	8 m	
	Configurable	No	
Detection area (angle)	120 °		

Classifications

ETIM 8.0	EC002955	ETIM 9.0	EC002955
ETIM 10.0	EC002955	ECLASS 14.0	27-11-06-92
ECLASS 15.0	27-11-06-92		