

WIL-BM-SK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Motion detector for the WIL-LED luminaire with screw connection. Switching time adjustable.

General ordering data

Order No.	2537720000
Type	WIL-BM-SK
GTIN (EAN)	4050118549157
Qty.	1 items

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	44	Depth (inches)	1.7323 inch
Height	33 mm	Height (inches)	1.2992 inch
Width	76 mm	Width (inches)	2.9921 inch
Net weight	29.04 g		

Temperatures

Operating temperature -20 - 60

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	82a8bf14-9104-4ca4-ab0c-226d976fdcac

Connection data

Connection thread	Terminal	Wiring	PIN 4: + (black), PIN 3: - (blue)
-------------------	----------	--------	-----------------------------------

Electric data

Rated voltage	24 V DC	Rated current	< 6.0 A
---------------	---------	---------------	---------

General technical data

Protection degree	IP20		
Dwell time, min.	1 min		
Dwell time, max.	10 min		
Detection range	min.	0 m	
	max.	8 m	
	Configurable	No	
Detection area (angle)	120 °		

Classifications

ETIM 8.0	EC000133	ETIM 9.0	EC000133
ETIM 10.0	EC000133	ECLASS 14.0	27-14-40-07
ECLASS 15.0	27-14-40-07		