

**WIL-BM-SK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Motion detector for the WIL-LED luminaire with screw connection. Switching time adjustable.

**General ordering data**

Order No.	2537720000
Type	<a href="#">WIL-BM-SK</a>
GTIN (EAN)	4050118549157
Qty.	1 items

**WIL-BM-SK**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	44	Depth (inches)	1.7323 inch
Height	33 mm	Height (inches)	1.2992 inch
Width	76 mm	Width (inches)	2.9921 inch
Net weight	29.04 g		

**Temperatures**

Operating temperature -20 - 60

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	82a8bf14-9104-4ca4-ab0c-226d976fdcac

**Connection data**

Connection thread	Terminal	Wiring	PIN 4: + (black), PIN 3: - (blue)
-------------------	----------	--------	-----------------------------------

**Electric data**

Rated voltage	24 V DC	Rated current	< 6.0 A
---------------	---------	---------------	---------

**General technical data**

Protection degree	IP20		
Dwell time, min.	1 min		
Dwell time, max.	10 min		
Detection range	min.	0 m	
	max.	8 m	
	Configurable	No	
Detection area (angle)	120 °		

**Classifications**

ETIM 8.0	EC000133	ETIM 9.0	EC000133
ETIM 10.0	EC000133	ECLASS 14.0	27-14-40-07
ECLASS 15.0	27-14-40-07		