

**THM ET TA 58/55 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system M-Print® PRO under Windows optimise all labelling efforts.

- High-quality polyester labels in different colours
- Due to their flexible material and the thick adhesive layer, the THM GEW can be used on angled or round objects such as cables or hoses
- Roll-packaged THM ET S7 can be used to label the Simatic 200S, S7-300 and S7-400 modules from Siemens
- Labels are automatically positioned in the printer for perfectly centred prints on each label.
- Labelling with the THM MultiMark or THM MultiMark Plus thermal transfer printers

**General ordering data**

Version	Conductor and cable markers, 58 x 55 mm, white
Order No.	<a href="#">2539390000</a>
Type	THM ET TA 58/55 WS
GTIN (EAN)	4050118570151
Qty.	1000 items

**THM ET TA 58/55 WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.35 mm	Depth (inches)	0.0138 inch
Height	58 mm	Height (inches)	2.2835 inch
Width	55 mm	Width (inches)	2.1654 inch
Net weight	1.22 g		

**Temperatures**

Operating temperature range	-50...100 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General data**

Version	Self-adhesive	Width	55 mm
UL 94 flammability rating	HB	Operating temperature range, max.	100 °C
Operating temperature range, min.	-50 °C	Colour	white
Halogen	No	Basic material	Polypropylene
Printed characters	without	Operating temperature range	-50...100 °C

**Conductor and cable markers**

Halogen	No
---------	----

**Classifications**

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**THM ET TA 58/55 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



## THM ET TA 58/55 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	RIBBON MM-HS 60/300 SW	Version	
Order No.	<a href="#">2448880000</a>	Ink ribbon	
GTIN (EAN)	4050118462944		
Qty.	1 ST		