

DG M20 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Intelligent cabling solutions can save you valuable time and money.

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread

Integration of operating and signalling devices into the seal possible

General ordering data

| | |
|------------|--|
| Version | Field Power® sealing insert, Seal with connection thread, IP65, with corresponding enclosure, EPDM |
| Order No. | 2545550000 |
| Type | DG M20 PT6 |
| GTIN (EAN) | 4050118555530 |
| Qty. | 1 items |

DG M20 PT6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E256877 |

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 19.5 mm | Depth (inches) | 0.7677 inch |
| Height | 33.8 mm | Height (inches) | 1.3307 inch |
| Width | 46.7 mm | Width (inches) | 1.8386 inch |
| Net weight | 20.77 g | | |

Temperatures

| | | | |
|---------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -40 °C...85 °C |
|---------------------|----------------|-----------------------|----------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|--|------------------------------------|---------------------------|-----------------------------|
| Basic material | EPDM | Silicone | No |
| Colour | black | Design | Seal with connection thread |
| Protection degree | IP65, with corresponding enclosure | UL 94 flammability rating | HB |
| Mounting position, installation notice | in FieldPower® sealing slot | Internal thread | M 20 |
| Version | Threaded adapter M20 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002624 | ETIM 9.0 | EC002624 |
| ETIM 10.0 | EC002624 | ECLASS 14.0 | 27-18-28-15 |
| ECLASS 15.0 | 27-18-28-15 | | |