

WQB 4 WTL 6/4 FF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | |
|------------|---|
| Version | Cross-connector (terminal), when screwed in, orange, 41 A, Number of poles: 4, Pitch in mm (P): 11.10, Insulated: Yes, Width: 40.4 mm |
| Order No. | 2550750000 |
| Type | WQB 4 WTL 6/4 FF |
| GTIN (EAN) | 4050118560619 |
| Qty. | 10 items |

WQB 4 WTL 6/4 FF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 5 mm | Depth (inches) | 0.1968 inch |
| Height | 29.32 mm | Height (inches) | 1.1543 inch |
| Width | 40.4 mm | Width (inches) | 1.5905 inch |
| Net weight | 4.2 g | | |

Temperatures

| | | | |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|-------|--------|--------|
| Basic material | Wemid | Colour | orange |
|----------------|-------|--------|--------|

System specifications

| | |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Type of fixing | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No | Type of mounting | when screwed in |

Dimensions

| | |
|-----------------|----------|
| Pitch in mm (P) | 11.10 mm |
|-----------------|----------|

General

| | | | |
|-----------------|---|---------------------|-----------------|
| Number of poles | 4 | Installation advice | Direct mounting |
|-----------------|---|---------------------|-----------------|

Rating data

| | |
|-----------------|------|
| Nominal current | 41 A |
|-----------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |