


WQB 12 WTL 6/4 FF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Version	Cross-connector (terminal), when screwed in, orange, 41 A, Number of poles: 12, Pitch in mm (P): 11.10, Insulated: Yes, Width: 129.1 mm
Order No.	2552080000
Type	WQB 12 WTL 6/4 FF
GTIN (EAN)	4050118577655
Qty.	10 items

WQB 12 WTL 6/4 FF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	29.32 mm	Height (inches)	1.1543 inch
Width	129.1 mm	Width (inches)	5.0827 inch
Net weight	24.11 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	orange
----------------	-------	--------	--------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

Dimensions

Pitch in mm (P)	11.10 mm
-----------------	----------

General

Number of poles	12	Installation advice	Direct mounting
-----------------	----	---------------------	-----------------

Rating data

Nominal current	41 A
-----------------	------

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		