

IE-PI-SCRJ-POF-QA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



FO SC inserts for plug-in connectors ver.1 / 4 / 14

General ordering data

Version	SC insert, Plug SCRJ, POF, reconnectable
Order No.	2564960000
Type	IE-PI-SCRJ-POF-QA
GTIN (EAN)	4050118574647
Qty.	10 items

IE-PI-SCRJ-POF-QA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	56 mm	Depth (inches)	2.2047 inch
Height	10.5 mm	Height (inches)	0.4134 inch
Width	13.2 mm	Width (inches)	0.5197 inch
Net weight	1.6 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

General data

Description of article	Plug SCRJ, POF, reconnectable	Colour	Miscellaneous
Housing main material	PA 66	Sheath diameter, max.	8 mm
Sheath diameter, min.	5 mm	Type of mounting	Screw mounting
Protection degree	IP67 with housing	Plugging cycles	≥ 500
Composition	Connector and flange insert for variant 1, 4 and 14 housings	Fibre type	POF
Insertion loss	≤ 1.0 dB	Connection 1	SCRJ
Connection 2	Screw	Single conductor diameter, min	2.1 mm
Ferrule material	Arcap	Dust protection cap material	TPE
Single conductor diameter, max	2.3 mm		

General standards

Connector standard	IEC 61754-24
--------------------	--------------

Classifications

ETIM 8.0	EC001122	ETIM 9.0	EC001122
ETIM 10.0	EC001122	ECLASS 14.0	19-17-01-22
ECLASS 15.0	19-17-01-22		