

HDC MBUS4 F AWG26-24**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Version	Crimp contact
Order No.	2565890000
Type	HDC MBUS4 F AWG26-24
GTIN (EAN)	4050118575446
Qty.	100 items

HDC MBUS4 F AWG26-24

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Dimensions and weights

Net weight

0 g

Temperatures

Limit temperature

-40 °C ... 90 °C

Environmental Product Compliance

RoHS Compliance Status

Compliant with exemption

RoHS Exemption (if applicable/known)

6c

REACH SVHC

Lead 7439-92-1

SCIP

6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

General data

Contact diameter, male Ø	1 mm	Stripping length, rated connection	4.5 mm
Type of connection	Crimp connection	Version insert	MBUS
Conductor cross-section, max.	0.25 mm ²	Conductor cross-section, min.	0.14 mm ²
Surface finish	gold	Plugging cycles	≥ 500
Type	Female	Basic material	Copper alloy
Series	ModuPlug	Production methods	turned
Material of contact	Copper alloy		

General data

Contact surface	Gold-plated	Transmission rate	100 MBit/s
Nominal current	4 A	Plugging cycles	≥ 500
Type	Female		

Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

Drawings

