
Data sheet

ES EPG 60/HPG AEH 95

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	Crimping tool insert, 95mm², Trapezoidal crimp
Order No.	2577870000
Type	ES EPG 60/HPG AEH 95
GTIN (EAN)	4050118590685
Qty.	1 items

ES EPG 60/HPG AEH 95

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	25 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Crimping width	22 mm	Crimp cross-section copper	95
Crimping width in mm	22		

Description of contact

Type of contact	Wire-end ferrules with/ without plastic collars	Conductor cross-section, max. AWG	3/0
Conductor cross-section, min. AWG	3/0	Crimping range, max.	95 mm²

tool data crimping

Crimping type/profile	Trapezoidal crimp	
Cable lug cross section	nominal	95 mm²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		